


Expert 2500



Technical Specifications

- > Hydraulic door closer with **rack and pinion** mechanism.
- > High quality components. Body manufactured with aluminium, arm and internal components manufactured with high quality steel.
- > Fix closing force EN3.
- > CE Certified according to European Standard EN 1154.
 - Certificate nº 2812 CPR AD5171
 - CE Classification
 - Door Mount Pull Side and Transom Mount Pull Side



1

Transom Mount Push Side

On security systems against fire, it is not allowed to install a door closer size EN2.

> Fire Resistant according to Eurpoean Standrad EN 1634-1.

3 8 3

- > Closing Speed Control. Adjustable closing speed by value in the range from 180° to 15°.
- > Latch Action Control. Ajustable latch action by valve in the range from 15° to 0°.















EN 3

≤ 950 mm ≤ 60 Kg




Individual Box

x 8

- > Thermostatic door closers. Closing time keeps stable submitted to temperatures between -15°C y +40°C.
- > Security against forced closings thanks to overpressure valve incorporated inside the door closer.
- > Adjustable Hold Open. Adjustable hold open system to any selected opening angle (optional).
- > High performance. Excellent closing efficiency by means of needle bearings incorporation.
- > Easy to install. Adapts to all type of applications and offers great ease of installation.
- > Range of colors. Available in five different colors: White (BL), Brown (BR), Black (NE), Gold (OR) and Silver (PL).




Hydraulic Controls



Latch Action Closing Speed

Dimensions



Technical Overview

Functional Performances				Installation Position		
Model	Adjustable Closing Speed	Adjustable Latch Action	Adjustable Hold Open	Door Mount Pull Side	Transom Mount Pull Side	Transom Mount Push Side
AD 2503 S	\checkmark	\checkmark		\checkmark	\checkmark	\checkmark
AD 2503 T	\checkmark	\checkmark	\checkmark	\checkmark	\checkmark	\checkmark

On fire doors, it is not allowed to install door closers with Hold Open device incorporated.



Guide Rail (With or Without Hold Open Function)

UCEM



Hold Open Device

DOM - MCM S.A.U. Artapadura, 12 01013 Vitoria-Gasteiz (Álava) Tel: +34 945 262 055 / +34 943 77 05 02



